

## Chemswab™ Presaturated Swab

**Product# CS25**

### Product Description

Chemswab Presaturated Swabs are general purpose, lint-free cleaning swabs. They are excellent for general purpose cleaning of computers, office and laboratory equipment. These highly effective cleaning swabs are ideal for cleaning sensitive surfaces, electronics components, touch keypads, keyboards, and instrument housings. Chemswab quickly and safely removes handling soils, dirt and oxides from PCB's, mechanical / electrical assemblies and other electronic equipment. Chemswab is especially effective in removing ink and permanent marker.

Chemswab Presaturated Swabs contain ultra-pure isopropyl alcohol (91% IPA / 9% Pure Water) on a urethane foam swab.

- Plastic Safe
- Dries Fast
- Leaves No Residue
- Nonabrasive
- Upper Ozone Safe; CFC/HCFC Free

### Typical Applications

Chemswab cleans and degreases:


- Keyboards and Touch pads
- Cables
- Cabinets and Housings

HANDLE: 1786B SBC #147 WHITE POLYPROPYLENE  
 MITT: A1455 3/16" WHITE CUSTOM FOAM  
 ADHESION: HOT MELTED HANDLE 1.4 LB.PULL



### Typical Product Data and Physical Properties

<b>Solubility in Water:</b>	Soluble
<b>Specific Gravity:</b>	0.81
<b>Evaporation Rate:</b> (ether =1)	<1
<b>Appearance:</b>	Clear, colorless liquid
<b>Flash Point (TCC):</b>	61° F (16.1°C)
<b>Percent Volatile</b>	100%
<b>Shelflife</b>	2 years
<b>RoHS Compliant</b>	Yes



## Chemswab™ Presaturated Swab

**Product# CS25**

### Compatibility

Chemswab Presaturated Swabs are generally compatible with most plastics, glass and metals. Compatibility must be checked with all antiglare coatings. As with any chemical product, component compatibility must be determined on a non-critical area prior to use.

Material	Compatibility
Aluminum	Excellent
Buna-N	Good
CPVC	Excellent
Epoxy	Excellent
Neoprene	Good
Noryl®	Excellent
Phenolic	Excellent
Cross-Linked PE	Good
Polycarbonate	Poor
Polypropylene	Good
Polystyrene	Poor
PVC	Fair
Teflon™	Excellent
Tygon™	Good
Viton™	Excellent

### Usage Instructions

**For industrial use only. Read SDS carefully prior to use.**

Remove wipe from packet and lightly wipe away any dust or contaminants from surfaces. Allow surface to dry completely before use.

### Availability

**CS25** 50 Premoistened Swabs individually packaged

### Environmental Impact Data

CFC	0.0%
HCFC	0.0%
CL Solv.	0.0%
VOC	91%
HFC	0.0%
ODP	0.0

CFC, HCFC, CL. SOLV., VOC, and HFC numbers shown are the content by weight. Ozone depletion potential (ODP) is determined in accordance with the Montreal Protocol and U.S. Clean Air Act of 1990. The ODP of this product is zero.

### Technical and Application Assistance

Chemtronics provides a technical hotline to answer your technical and application related questions.

*The toll free number is: 1-800-TECH-401.*

### Note:

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. CHEMTRONICS does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.