



All dimensions are in mm; tolerances according to ISO 2768 c

General Information

Magnetic RJ45 PoE+ featured extension cable with magnetic break-off interface

Magnetic interface can mate with

- Magnetic RJ45 adapter cable (L99-M0043-XXX-Y)
- Magnetic RJ45 adapter cable (L99-M0017-XXX-Y)
- Standard RJ45 (8P8C) male connector

Available Length

Description	Length "A" in [mm] ¹
L99-M0018-XXX-Y	XXX ± 1%

¹length < 300 ± 3 mm

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RF_35/09.14/6.2

Available Colour

Description	Colour "Y" in
L99-M0018-XXX-Y	A- white, similar RAL 9010
	B- black, similar RAL 9005
	C- grey, similar RAL 7031

Material and Plating

RJ45 extension cable

Magnetic connector housing	PC+ABS	See colour table
Magnets	NdFeB	Nickel plated
Fixing pin	Brass	Non-plated
RJ45 Male	RJ45 8P8C	Contacts gold plated
Cable	LSNH	See colour table
RJ45 Male	RJ45 8P8C	Contacts gold plated
Bending protection	TPE	See colour table

Connectors

8P8C Male	ISO/ IEC 11801, IEC 60603-7-51, IEC 60512-99-001
Cable	Cat 6A S/FTP, 4 x 2 x AWG26, outer diameter 6.8 mm

Electrical Data

Ethernet characteristics	1 Gbit/s (IEEE 802.3 ab) Power over Ethernet (15,4 Watt) (IEEE 802.3 af) Power over Ethernet Plus (25,4 Watt) (IEEE 802.3 at) Category 5e with class D up to 100 MHz
Voltage resistance	1.000 V DC between data lines 1.500 V DC between data lines and shield
Insulation resistance	≥ 500 MΩ at 100 V DC
Contact resistance	Typically ≤ 20 mΩ (accord. to IEC 60512 2a)
Pin assignment	According to EIA/TIA-568B 1:1 assignment from plug to plug at each cable end

Magnetic RJ45

Extension cable

L99-M0018-XXX-Y

Mechanical Data

Disengagement force of magnetic connection in straight direction ≥ 20 N

Mating cycles magnetic connection with resistive load 750

Environmental Data

Temperature range -25°C to 50°C
Please note:
Magnets can start losing their magnetic properties above 60 °C

Compliance

RoHS Compliant



Compliant

Packing

Standard 1 pce in pressure lock bag
1 bag in carton box

Weight Depending on cable length

Caution!

Magnets can impact the function of pace makers and implantable cardioverter-defibrillators (e.g. actuation of reed switch). Keep a minimum distance of 0.2 m (20 cm) between the magnetic connector and the implanted devices to prevent malfunction and danger to health.

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
M. Portenkirchner	10.01.17	H. Wurm	08.10.19	a00	19-s248	S. Kirchhofer	15.10.19